





NOTES :

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY
2. MATERIAL: BODY -- MAPEX UL94 -V0, BLACK
M8 x 1.25 STUD -- SAE1215/DIN 95Mn28/11SMn30 STEEL, ZINC PLATED
3. MAXIMUM MOUNTING TORQUE FOR M4 MOUNTING HOLES 10 N*M, 7.4 LBF*FT
4. MAXIMUM TORQUE FOR M8 STUD 8.9-13.3 LBF*FT, 12-18 N*m

METRIC

ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES	UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
⊙	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

[illegible]