


APPLICABLE SAE STANDARD OR
RECOMMENDED PRACTICE SAE J2599

8-59

MM	IN
19.05	.750
22.22	.875
23.87	.940
36.57	1.440
47.49	1.870
57.91	2.280



METRIC

NOTES:

1. 8367 ADAPTER FACE NUT PERMITS
ASSY OF SWITCH TO 19.05 & 22.22
DIA. PANEL HOLES.
2. 250 KEY COMBINATIONS; REMOVABLE
IN BOTH POSITIONS.
3. ALL STEEL PARTS PLATED.

DO NOT SCALE

[illegible]

CH-188(4-78)