






TOP

RATINGS:

MAXIMUM VOLTAGE . 44,000 Vac
 MAXIMUM CURRENT . 220 mA
 RESISTANCE 200 k Ω
 THERMAL 1 MINUTE ON
 120 MINUTES OFF



FRONT



RIGHT SIDE

NOTES:

1. DIMENSIONS IN MILLIMETRES (INCHES).
2. TERMINAL-BLOCK SCREWS: 6-32 x 0.25.
3. MOUNTING SCREWS: M6 OR 0.25-20.
4. USE LIQUID-TIGHT GLAND FOR
 TERMINAL-BLOCK-ENCLOSURE CABLE ENTRY.

ER-72KV SENSING RESISTOR