

COLE-HERSEE CO.


IN.  
0.25 .040  
1.17 .440  
3.75 .740  
5.57 .810  
6.57 1.440  
10.00 1.890

EX 23484

APPLICABLE SAE STANDARD OR  
RECOMMENDED PRACTICE SAE J259

LEVER, ZINC DIE CAST, CLEAR DICHROMATE W/P

95612-02



| LEGEND |          |
|--------|----------|
| I      | IGNITION |
| S      | START    |
| B      | BATTERY  |

|                 |         |
|-----------------|---------|
| START           | 20 AMPS |
| IGN             | 25 AMPS |
| RATING @ 12V DC |         |

# NOTES

- 1 SILVER LAMINATED CONTACT SURFACES
- 2 MELAMINE LINER.
- ③ ALL STEEL PARTS PLATED

4.0" RING SEALED AT BUSHING.

METRIC

|     |     |      |    |     |            |         |          |               |                           |         |        |       |                |
|-----|-----|------|----|-----|------------|---------|----------|---------------|---------------------------|---------|--------|-------|----------------|
| LET | WAS | DATE | BY | LET | WAS        | DATE    | BY       | MATERIAL      | DRAWN                     | CHECKED | APPR'D | SCALE | DATE DRAWN     |
|     |     |      |    |     |            |         |          | NOTED         | RO                        | Re      |        | FULL  | 5-2-89         |
|     |     |      |    |     |            |         |          | FINISH        | COLE-HERSEE COMPANY       |         |        |       | DATE BLUEPRINT |
|     |     |      |    |     |            |         |          | NOTED         | BOSTON, MASS 02127, U.S.A |         |        |       |                |
|     |     |      |    | AI  | 11/1       |         |          | TOLERANCES    | HEAVY DUTY WEATHERPROOF   |         |        |       | 95612-02       |
|     |     |      |    | A   | AD OR ZINC | 25234   | 12/10/90 | FRACTIONAL ±  | 3 POS IGN & START SWITCH  |         |        |       |                |
|     |     |      |    |     | ISSUED     | 5/10/89 | AF       | DECIMAL ±0.25 |                           |         |        |       |                |