


MM	IN.
125	.010
3.17	.125
6.35	.250
22.09	.870
47.24	1.860
67.31	2.650


COLE-HERSEE CO.

95532

APPLICABLE SAE
STANDARD OR RECOMMENDED
PRACTICE SAE J259



Confidential Property of Cole Hersee



NOTE:
① ALL STEEL PARTS PLATED

METRIC

LET			WAS			DATE			BY			MATERIAL			DRAWN			CHECKED			APPR'VD.			SCALE			DO NOT SCALE					
												— # —			PH			TY 5-6-77						1:1			DATE DRAWN					
			M			ECN 06023			2/2/66			S															12-11-61					
			L			CAD OR ZINC 125234			11/17/92			JH			FINISH												DATE BLUEPRINT					
			K			ECN 2339A			2-2-87			1/2			— # —						COLE-HERSEE COMPANY											
																					BOSTON, MASS. 02127, U.S.A.											
			W			EXA/19872			3-8-77			1/2			TOLERANCES																	
			H			REV. 19872			5-6-77			1/2			FRACTIONAL ±																	
															DECIMAL ±.25																	
																								2 POSITION								
																											IGNITION SW.			95532		