



MM IN
 8.48 .334
 8.55 .337
 11.43 .45
 6.35 .25
 34.92 1.375
 41.27 1.625

METRIC

75228-03



FRONT VIEW OF KNOB

NOTE 1
 (A)

11.43



RETAINER (B)

7/16 - 28 UNEF MTG. STEM

HEX NUT

5' PROOF L' WASHER

6 35 MALE BLADE TERMS. TYP



41.27
 REF.

NOTE:

1. PUSH KNOB TO ACTIVATE WASHER CIRCUIT
 PARK, LOW, HIGH POSITIONS
- 2 ALL STEEL PARTS PLATED

12VOLTS @ 10 AMPS

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	BASIC 02 WITH KNOB	DATE DRAWN
									EA	RFB		1=1		3-25-83
				C	ECN 24372	6/7/90	BL	FINISH						DATE BLUEPRINT
				B	SEN 23542	12-12-86	2U							
				A	22545	10-5-84	AK	TOLERANCES						
					ISSUED	1/2/83	RF	DECIMAL ± .010 METRIC ± .25						
													3 POS ROTARY SW	75228-03

CH-188(4-78)