

Ø33.2 ± 0.18
[Ø1.306 ± 0.007]

4.8 ± 0.08
[0.188 ± 0.003]

7.9 ± 0.13
[0.312 ± 0.005]

95.50 ± 1.59
[3.760 ± 0.063]

90.73 ± 1.59
[3.572 ± 0.063]

112.2 ± 1.59
[4.416 ± 0.063]

74.1 ± 1.59
[2.916 ± 0.063]

25.4 ± 0.20
[1.000 ± 0.008]

REVISION

REV	DATE	DESCRIPTION
A	7/19/23	526717GCP - RELEASE MRY

1					
NO	COMPONENT NO	DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL					
<S>		CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●		DENOTES CRITICAL CHARACTERISTICS.			
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
⬡ST		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			
MATL SPEC			FINISH		
DRW JMoler		DATE 6/23/2023		SCALE NTS	FINISH GOOD WT GRAMS/PIECE
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994					
3RD ANGLE PROJECTION					
TITLE L60S 125-200A OUTLINE					
 Littelfuse® CHICAGO, ILLINOIS 60631		REVISION A		DRWG NO. OL-L60S200	
				SHEET 1 OF 1	