


- NOTES:
1. MAX. RATING 30A, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. WIRE: 12 GA, COLOR: ORANGE

CUSTOMER: FORD
CUSTOMER P/N: 1W1T-14517-AA

NO		COMPONENT NO	DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL						
COPIES TO		MATL SPEC		FINISH		
1	9	18	DRW	CR	DATE	01/24/00
2	10	19	CHK		DATE	1:1
3	12	20			DATE	SUPER DRW
4	13	21	APPD		DATE	RAW STK WT
5	14	23				LBS/M
6	15	33				
7	16	43				
8	17	53				
TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.01 THREE PLACE DEC ±.005 ANGULAR ±1°						
MINIFUSE HOLDER, IN LINE						
LTR		REVISION				CHK APD
A		60197-RELEASE 01/24/00 PJM				
B		80686D-CHG 26.7 TO 27.1 & 21.6 TO 23.6 07/07/00 PJM				



OUTLINE
01530024Z
B

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
DENOTES CRITICAL CHARACTERISTICS.
DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE ----
DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.-PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IS LOCATED IN THE LITTELFUSE INSPECTION INSTRUCTIONS.
DENOTES CP DIMENSIONS.-MINIMUM CP VALUE ----
DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS NOTED IN THE DIMENSIONAL LIMITATIONS LOCATED TO THE RIGHT OF THIS CHARACTERISTIC FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT