



MM	IN.
.25	.010
2.25	.090
12.70	.500
15.71	.540
17.01	.670
17.27	.680
21.08	.830
27.94	1.100
28.44	1.120
30.22	1.190
31.49	1.240
34.83	1.450
44.45	1.750



COLE-HERSEE CO.



MOUNTING HOLE DETAIL



ROCKER, WHITE
BEZEL, STEEL, NICKEL PLT., BRIGHT FINISH
INSULATOR, MOLDED PHENOLIC
MALE BLADE TERM., BRASS SAE J858 TYPE 1B (6 REQ'D)



METRIC

NOTES:
1) 25 AMPS @ 12 VDC LAMP LOAD
2) SILVER CONTACT RIVETS AND SILVER CONTACT PAD.

57006-06 SAME AS 57006-02 EXCEPT BEZEL NICKEL PLT. DULL FINISH.

HEAVY DUTY

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	BASIC WITH WIDE BEZEL	DATE DRAWN
								—#—	KG	TY	83/76	1:1		7-30-76
								FINISH					COLE-HERSEE COMPANY	DATE BLUEPRINT
								TOLERANCES					BOSTON, MASS. 02127, U.S.A.	
								FRACTIONAL ±					DOUBLE POLE DOUBLE THROW	57006-02
								DECIMAL ±					ROCKER SWITCH	57006-06