





2.5	.010
2.28	.090
12.70	.500
13.71	.540
17.01	.670
17.27	.680
21.08	.830
22.86	.900
27.94	1.100
30.22	1.190
31.49	1.240
36.83	1.450
39.87	1.570

57003-01
57003-05

METRIC

NOTES:

1. SILVER CONTACT SURFACES.
2. HEAVY DUTY.
3. 25 AMPS @ 12 V DC LAMP LOAD.
4. ALL STEEL PARTS PLATED.
5. ALL DIM'S. ARE REF. ONLY.

DO NOT SCALE

57003-05 SAME AS 57003-01
EXCEPT BEZEL NICKEL PLATE
DULL FINISH

[illegible]

CH-188(4-78)