




MM	IN
25	.010
228	.090
8.63	.340
17.01	.670
17.27	.680
21.08	.830
22.86	.900
27.94	1.100
30.22	1.190
31.49	1.240
36.83	1.450
39.87	1.570

METRIC

NOTES:

1. SILVER CONTACT SURFACES.
2. HEAVY DUTY.
3. 25 AMPS @ 12 VDC LAMP LOAD.
4. ALL STEEL PARTS PLATED.
5. ALL DIM'S ARE REF. ONLY.

56006-05 SAME AS 56006-01
EXCEPT BEZEL NICKEL PLT.
DULL FINISH

[illegible]

CH-188(4-78)