






NOTE:

ALL DIMENSIONS ARE IN MILLIMETERS,
ENGLISH DEMENSIONS ARE IN [].

CERTIFICATION OF
COUNTRY OF ORIGIN
REQUIRED

MAT'L. SPEC.		Nylon Cover: Black	
FINISH		SCALE	
DR. GES. Dr. 7.94		SUPER. DR.	
CHK. [Signature]		DATE 10-11-94	
APPD. [Signature]		RAW STK. WT.	
TOLERANCE UNLESS OTHERWISE SPECIFIED		LBS./M	
TWO PLACE DEC. $\pm .50$ mm [0.020]		FRACTION $\pm$	
THREE PLACE DEC. $\pm .25$ mm [0.010]		ANGULAR $\pm$	
TITLE 4 POSITION MAXI FUSE MODULE			
Littelfuse 800 E. NORTHWEST HIGHWAY DES PLAINES, ILLINOIS 60016			
DRWG. NO. 03540505Z			

LTR	REVISION	CHK.	APPD.
A	06534 - RELEASED October 10, 94 GES.	[Signature]	[Signature]
B	36644D - CHG - 2 PLACE TOLERANCE .010 TO .020 CHG - 2 PLACE TOLERANCE .020 TO .010 2-10-95 JCU	[Signature]	[Signature]
C	36988C - ADD METRIC DIM'S 7-19-95 RFR	[Signature]	[Signature]
D	37085D - CHG TITLE 8-19-98 JCU	[Signature]	[Signature]
E	000807ER - 10-9-07 REINSTATE JCU		