

# 58027 SERIES ROCKER SWITCHES



## Description

Littelfuse Rocker Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

The 58027 Series is our most popular line of unlit rocker switches. These products are single-actuator switches that are commonly used for in-cabin controls, but are IP66 rated against dust and moisture.

## Web Resources

Download 2D print and technical resources at:

[littelfuse.com/58027](http://littelfuse.com/58027)

## Ordering Information

| PART NUMBER | DESCRIPTION                     | CIRCUITRY | ACTUATOR                                 | POSITIONS                                          | TERMINATION    |
|-------------|---------------------------------|-----------|------------------------------------------|----------------------------------------------------|----------------|
| 58027-01 *  | Single, Dependent Rocker Switch | SPST      | 2-position, matte black plastic actuator | On - Off (Up-Down)                                 | 2 Brass Blades |
| 58027-04 *  | Single, Dependent Rocker Switch | SPDT      | 3-position, matte black plastic actuator | Momentary On - Off - Momentary On (Up-Center-Down) | 3 Brass Blades |
| 58027-06 *  | Single, Dependent Rocker Switch | DPST      | 2-position, matte black plastic actuator | Off - On (Up-Down)                                 | 4 Brass Blades |
| 58027-11 *  | Single, Dependent Rocker Switch | DPDT      | 3-position, matte black plastic actuator | On - Off - Momentary On (Up-Center-Down)           | 6 Brass Blades |

\* Box and Retail Blister Pack Available

## Features and Benefits

- Silver contacts for corrosion resistance.

## Specifications Overview

|                            |                                                                                                |
|----------------------------|------------------------------------------------------------------------------------------------|
| <b>Voltage Rating:</b>     | 25A @ 12V DC<br>15A @ 24V DC                                                                   |
| <b>Housing:</b>            | Black Plastic                                                                                  |
| <b>Mounting:</b>           | Snap-in matte black bezel through 21.1mm x 36.8mm rectangular Panel Hole, 2.4mm to 4.7mm thick |
| <b>Ingress Protection:</b> | IP66 (Contact Area)                                                                            |

## Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

## Dimensions

