




RESISTANCE @ +25°C = 3,000 Ω $\pm$ 10%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)
 THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +150°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	11/03/11	DD

SCALE	NONE	© COPYRIGHT	
DRAWN BY	DAN DANKERT	U.S. SENSOR CORP.	
DATE	10/08/93	714-639-1000 www.ussensor.com	
REV.	NONE	NTC THERMISTOR	
LAYER	0 OF 1	P/N	LC302J2K