

# Military Midget 10x38 mm Fuses

## 593 Series

Commercial Equivalent = [FLM Series](#)



### Description

With a vast network of manufacturing and engineering facilities and a global system of distribution channels, Littelfuse offers a variety of switchgear fuses to meet your specific needs, including military high-reliability fuses.

### Features & Benefits

FEATURES	BENEFITS
<b>10x38 mm size</b>	Common dimensions used in a variety of applications
<b>Time-delay</b>	Allows for temporary current surge for a short period of time without blowing
<b>Fiberglass body</b>	Cost effective materials provide a lower cost alternative for supplemental circuit protection
<b>POWR-GARD® technology</b>	Ensures quality overcurrent protection

### Applications

- Control circuits transformers
- Solenoids
- Circuits with high in-rush currents
- Small motors

### Approved to MIL-PRF-15160

MIL TYPE DESIGNATION	NICKEL-PLATED CAPS
F09B 250V 3/10A	<b>593.300</b>
F09B 250V 4/10A	<b>593.400</b>
F09B 250V 1/2A	<b>593.500</b>
F09B 250V 6/10A	<b>593.600</b>
F09B 250V 8/10A	<b>593.800</b>
F09B 250V 1A	<b>593.001</b>
F09B 250V 1 1/8A	<b>593.1.12</b>
F09B 250V 1 1/4A	<b>593.1.25</b>
F09B 250V 1 3/10A	<b>593.01.4</b>
F09B 250V 1 1/2A	<b>593.01.5</b>

# Military Midget 10x38 mm Fuses

## 593 Series

### Approved to MIL-PRF-15160

MIL TYPE DESIGNATION	NICKEL-PLATED CAPS
F09B 250V 1 $\frac{1}{10}$ A	<b>593</b> 01.6
F09B 250V 1 $\frac{1}{10}$ A	<b>593</b> 01.8
F09B 250V 2A	<b>593</b> 002
F09B 250V 2 $\frac{1}{4}$ A	<b>593</b> 2.25
F09B 250V 2 $\frac{1}{2}$ A	<b>593</b> 02.5
F09B 250V 2 $\frac{9}{10}$ A	<b>593</b> 02.8
F09B 250V 3A	<b>593</b> 003
F09B 250V 3 $\frac{1}{10}$ A	<b>593</b> 03.2
F09B 250V 3 $\frac{1}{2}$ A	<b>593</b> 03.5
F09B 250V 4A	<b>593</b> 004
F09B 250V 4 $\frac{1}{2}$ A	<b>593</b> 04.5
F09B 250V 5A	<b>593</b> 005
F09B 250V 5 $\frac{1}{10}$ A	<b>593</b> 05.6
F09B 250V 6A	<b>593</b> 006
F09B 250V 6 $\frac{1}{4}$ A	<b>593</b> 6.25
F09B 250V 7A	<b>593</b> 007
F09B 250V 8A	<b>593</b> 008
F09B 250V 9A	<b>593</b> 009
F09B 250V 10A	<b>593</b> 010
F09B 125V 12A	<b>593</b> 012
F09B 125V 15A	<b>593</b> 015
F09B 32V 20A	<b>593</b> 020
F09B 32V 25A	<b>593</b> 025
F09B 32V 30A	<b>593</b> 030

Note: Boldface numbers indicate series; light type numbers indicate amperage value.

**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).