



74600-02

MM	IN
11.43	.450
22.42	.883
41.70	1.641
75.00	2.950
0.8mm ²	18GA
3.86	.152
4.01	.158
6.37	.251
6.43	.253
8.50	.335
8.63	.340



NEGATIVE GROUND ONLY

METRIC



FRONT VIEW OF KNOB

- NOTES:
1. 12 VOLTS D.C. (14.7 VOLTS MAX)
4 AMPS MAX (UNIT NOT LOAD SENSITIVE)
LAMP OR RESISTIVE LOAD NEGATIVE GROUND ONLY
(GROUND WIRE (BLACK) MUST BE GROUNDED)
 2. PROTECTED FOR REVERSE POLARITY (30 V D.C.)
 3. WEATHERPROOF SEALED
 4. ALL STEEL PARTS PLATED

WIRE COLOR	CIRCUIT
BLACK	GROUND
WHITE	LOAD
RED	BATTERY

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECK'D	APPR'D	SCALE	DATE DRAWN
									VAK			1:1	10-3-84
				C	ECN 24372	6/11/86	BL	FINISH					DATE BLUEPRINT
				B	ECN 23482	4/8/87	LZ						
				A	23272	10-21-86	AF	TOLERANCES					
					ISSUED	1/31/88	CS	DECIMAL ±	SWITCH, DIMMER, 4 AMP				74600-02
								METRIC ±					

CH-18014-781