

# New Littelfuse & Cole Hersee Retail Packaged Product Offerings

Additional popular Littelfuse and Cole Hersee products are now in retail blister packaging enabling showroom and retail display.

## SR Series Master Battery Disconnect Switch



**Part No: 880062-BP**

- 300A at 32V DC
- 3500A Max Current Rating
- 300A Continuous Current & 3500A for 2 Second Intermittent Current
- SPST, ON-OFF
- IP67 / IP69K Ingress Protection
- Stainless Steel Hardware and 3/8" -16 Tin-Plated Copper Studs

[Littelfuse.com/SR](http://Littelfuse.com/SR)

## Continuous Duty Solenoid Relay



**Part No: 24213-BP**

- 200A at 12V DC
- SPST, Continuous Duty
- Terminals:  
Two Steel 5/16" -24 studs,  
Two Steel #10-32 studs
- Silver plated contacts

[Littelfuse.com/ContinuousDuty](http://Littelfuse.com/ContinuousDuty)

## 2484 Series Battery Disconnect Switch



**Part No: 2484-BP**

- Continuous Current: 40A at 6V DC, 20A at 12V DC
- Intermittent Current: 250A at 6V DC, 125A at 12V DC
- 6-12V DC, Two Position, SPST
- Terminals: Two copper 3/8" -24 studs

[Littelfuse.com/2484](http://Littelfuse.com/2484)

## Solenoid Continuous Duty Reversing Relay



**Part No: 24450-BP**

- 75A at 12V 5 min ON/5 min OFF, 125A at 12V 30 sec, 150A at 12V 0.5 sec
- Intermittent Duty, DPDT, Normally Open
- With dynamic braking capability
- Four 5/16" -24 Copper Studs

[Littelfuse.com/RevSolenoid](http://Littelfuse.com/RevSolenoid)

## 956 Heavy Duty Series Rotary Ignition Switch



**Part No: 956-3126-BP**

- 3 Position: Off-Ign/Acc-Ign/Start
- Rated up to 10A at 12V
- 4 Brass Screw Terminals
- Start Lockout: Switch must go to OFF position before the start circuit can be re-energized
- Fits panels up to 0.76" (2.28mm) thick
- Complies with SAE J259

[Littelfuse.com/956Series](http://Littelfuse.com/956Series)

## Standard Heavy Duty Weather Resistant Toggle Switch



**Part No: 5582-10-BP**

- SPST: Single Pole, Single Throw, On-Off
- Rated up to 25A at 12V DC
- Mounting: 15/32" -32 thread, 15/32" (11.90mm) long
- Fits panels up to 1/4" (6.35mm) thick
- 2 Wire Leads, 8" long (203.2mm), 16AWG
- Nickel-plated brass handle 0.69" (17.52mm)

[Littelfuse.com/StandardDuty](http://Littelfuse.com/StandardDuty)

### MEGA Flex Series

#### MEGA® Bolt-Down Fuse Block



Part No: 02981028-BP

- Rated for MEGA fuses 500A at 32V DC
- Flexible cover allows for universal installation
- Dovetail locks allow holders to stack
- M8 Terminal Studs
- M6 Mounting Holes

[Littelfuse.com/Mega-Flex](http://Littelfuse.com/Mega-Flex)

### MIDI Flex Series

#### MIDI® Bolt-Down Fuse Block



Part No: 04981038-BP

- Rated for MIDI fuses up to 200A at 32V DC
- Flexible cover allows for universal installation
- Dovetail locks allow holders to be stacked
- M5 Terminal Studs
- M4 Mounting Holes

[Littelfuse.com/Midi-Flex](http://Littelfuse.com/Midi-Flex)

### MAH Series

#### MAXI Style In-Line Fuse Holder



Part No: MAHC-BP

- Rated for MAXI fuses 20 to 60A at 32V DC
- 5" UL3288 Wire Leads
- Designed for medium current loads
- In-Line holders allow for universal mounting

[Littelfuse.com/MAH](http://Littelfuse.com/MAH)

### MIDI-498 Series

#### MIDI Bolt Down Fuse Block



Part No: 04980903-BP

- Rated for MIDI fuses 30 to 200A at 32V DC
- Dovetail locks allow holders to be stacked
- M5 Terminal Studs
- M4 Mounting Holes

[Littelfuse.com/Midi-498](http://Littelfuse.com/Midi-498)

### Sealed ATO In-Line Series

#### Sealed HD ATO In-Line Fuse Holder



Part No: FHAS100-BP

- Rated for ATO fuses up to 30A at 32V DC
- Rated IP67 with sealed cover for moisture & dust resistance
- Includes two tinned 8" Red GXL wire leads for easy in-line installation

[Littelfuse.com/SealedATO-MINI](http://Littelfuse.com/SealedATO-MINI)

### Sealed MINI In-Line Series

#### Sealed HD MINI In-Line Fuse Holder



Part No: FHMS200-BP

- Rated for MINI fuses up to 30A at 32V DC
- Rated IP67 with sealed cover for moisture & dust resistance
- Includes two tinned 8" Red GXL wire leads for easy in-line installation

[Littelfuse.com/SealedATO-MINI](http://Littelfuse.com/SealedATO-MINI)

### Commercial and Fleet Vehicle

#### Emergency Fuse Kit



Part No: 00941003Z

- This convenient kit contains the popular amperage fuses for most vehicle types along with two fuse pullers

### Trailer Connector Holder

#### Universal 7P and 13P



Part No: 11750-BP

- Stores plugs while not in use and extends electrical connection life by keeping contacts free from dirt and water
- Impact-resistant, heavy duty glass-filled housing is spring loaded for secure locking

[Littelfuse.com/11750](http://Littelfuse.com/11750)