



# CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC24002424257

Valid from: Mar.14,2024

Valid until:Feb.28,2029

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** Littelfuse, Inc  
8755 W Higgins Rd #500, Chicago, IL 60631

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** Littelfuse, Inc  
8755 W Higgins Rd #500, Chicago, IL 60631

**NAME AND LOCATION OF THE FACTORY** Zhejiang Meishuo Electric Technology Co.,LTD  
No.158 Wei 12th Road,Yueqing Economic Development Zone Yueqing city Zhejiang P.R. China

**PRODUCT NAME, MODEL AND SPECIFICATION** relay  
EVR series , main contact load: 35A 125VAC/220VAC/250VAC/277VAC; 40A 125VAC/220VAC/250VAC/277VAC Connect 10A current carrying 40A and disconnect 10A125VAC/220VAC/250VAC/277VACNC Auxiliary contact load: 1A125VAC/220VAC/250VAC/277VAC Coil: 6VDC, 9VDC, 12VDC, 24VDC, 1.88W; Electrical lifespan: 5E4 cycles (35A 90 °C); 1E4 cycle (40A 85 °C) 5E4 cycle (connect 10A current carrying 40A and disconnect 10A 85 °C) 1E5 cycle (1A 90 °C) Mechanical life: 1E6 cycles; Environmental temperature: -40 ° C~85 °C, -40 ° C~90 ° C RT I RT II RT III

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** GB/T 21711.1-2023

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462155-2010.  
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGNATURE:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.  
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666  
<http://www.cqc.com.cn>



# CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC24002424257

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

## 二. 系列命名规则:

EVR	-	2	A	12V	-	1
I		II	III	IV		V

I、产品型号: EVR

II、主触点组数: 2 为 2 组

III、触点形式: A: 表示两组常开主触点, 不带辅助触点  
B: 表示两组常开主触点和一组常闭辅助触点。

IV、线圈电压: 6、9、12、24VDC (标注于铭牌合适位置)

V、绝缘等级F, 用1表示



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE