



TOP

**RATINGS:**  
 MAXIMUM VOLTAGE . 44,000 Vac  
 MAXIMUM CURRENT . 220 mA  
 RESISTANCE . . . . . 200 kΩ  
 THERMAL . . . . . 1 MINUTE ON  
 120 MINUTES OFF



FRONT



RIGHT SIDE

**NOTES:**

1. DIMENSIONS IN MILLIMETRES (INCHES).
2. TERMINAL-BLOCK SCREWS: 6-32 x 0.25.
3. MOUNTING SCREWS: M6 OR 0.25-20.
4. USE LIQUID-TIGHT GLAND FOR TERMINAL-BLOCK-ENCLOSURE CABLE ENTRY.

**ER-72KV SENSING RESISTOR**