



| REVISION |         |                         |
|----------|---------|-------------------------|
| REV      | DATE    | DESCRIPTION             |
| A        | 6/16/23 | 526604GCP - RELEASE MRY |

| 1   | COMPONENT NO   | DESCRIPTION  | QTY/M                         | U/M          |
|---|--|--------------|-------------------------------|--------------|
| <b>BILL OF MATERIAL</b>   |  |              |                               |              |
| <S>   | CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE   |              |                               |              |
| ●   | DENOTES CRITICAL CHARACTERISTICS.  |              |                               |              |
| CPK   | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE   |              |                               |              |
| Ⓢ   | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS. |              |                               |              |
| CP  | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.               |              |                               |              |
| MATL SPEC   |  |              | FINISH                        |              |
| DRW<br>JMoler   | DATE<br>5/24/2023  | SCALE<br>NTS | FINISH GOOD WT<br>GRAMS/PIECE |              |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994 |  |              |                               |              |
| 3RD ANGLE PROJECTION  | <b>TITLE</b><br>KLC 1-30A OUTLINE  |              |                               |              |
|   |  |              |                               |              |
|   |  | REVISION     | DRWG NO.                      | SHEET 1 OF 1 |
| CHICAGO, ILLINOIS 60631   |  | A            | OL-0KLC030                    |              |

A