


# 277 IN-LINE SERIES

## 32V 20A IN-LINE BLADE FUSE HOLDER



277.6106.0002

### Description

The 277 In-Line Series 32V 20A In-Line Blade Fuse Holder is available for ATO® blade fuses as well as FKS fuses and is compatible with fuses rated up to 20A (fuses sold separately). The easy-to-install in-line fuse holder handles up to 15A of continuous current. A waterproof 277 In-Line Series fuse holder model featuring red wire leads is available.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/277InLine](https://littelfuse.com/277InLine)

### Specifications

|                                   |                     |
|-----------------------------------|---------------------|
| <b>Current Rating Continuous:</b> | 15 Amps             |
| <b>Current Rating Max:</b>        | 20 Amps             |
| <b>Fuse Type:</b>                 | ATO, FKS Fuses      |
| <b>Mounting Method:</b>           | In-Line Fuse Holder |
| <b>Max Voltage Rating:</b>        | 32 VDC              |

### Applications

- Automotive Circuit Protection
- Accessory Circuits

### Features and Benefits

- Accepts fuses rated up to 20A (fuses sold separately)
- Handles up to 15A of continuous current
- Available for ATO® blade fuses and FKS fuses
- Waterproof fuse holder model with a tetherable, sealed cover and 2.5 mm<sup>2</sup> red PVC FLY HT105° ISO 6722 wire leads is available

### Ordering Information

| PART NUMBER   | DESCRIPTION   | CURRENT RATING MAX | FUSE TYPE | MOUNTING METHOD    | MAX VOLTAGE RATING |
|---------------|---|--------------------|-----------|--------------------|--------------------|
| 277.6106.0002 | 32V 20A In-Line Blade Fuse Holder for FKS Fuses             | 20 Amps            | FKS Fuse  | In-Line Fuseholder | 32VDC              |
| 277.6306.0001 | 32V 20A Waterproof In-Line Blade Fuse Holder for ATO® Fuses | 20 Amps            | ATO Fuse  | In-Line Fuseholder | 32VDC              |