

ATO® AFH Series

32V In-Line Wire-Leaded Panel-Mount Fuse Holder



Description

The ATO® AFH Series 32V In-Line Wire-Leaded Panel-Mount Fuse Holder can be used for either in-line installation or panel-mounting applications thanks to the 8" looped lead wire and the snap fit gripping arms.

Designed with a 14 AWG black lead wire, the ATO® AFH Series fuse holder is compatible with ATO® blade-style fuses (sold separately) up to 20 amps. The interlocking, heat-stabilized nylon fuse holder body allows you to snap multiple fuse holders together.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/AFHFuseHolders

Ordering Information

PART NUMBER	DESCRIPTION	MAX CURRENT RATING	MAX VOLTAGE RATING	WIRE SIZE	FUSE TYPE	PACKAGING / QUANTITY
0AFH0001XP	In-Line Wire-Leaded Panel-Mount Fuse Holder	20A	32V DC	14 AWG	ATO	Blister Pack - 100 Pcs
0AFH0001Z W/O FUSE	In-Line Wire-Leaded Panel-Mount Fuse Holder	20A	32V DC	14 AWG	ATO	Bulk - 1 Pcs

Fuses Sold Separately

Specifications

Continuous Current Rating:	15A
Max Current Rating:	20A
Max Current Rating Terminal:	20A
Fuse Type:	ATO®
Flammability Rating:	UL 94 V-2
Mounting Method:	In-line Fuse Holder
Output Terminals:	Wire with Terminals Included
Max Voltage Rating:	32V DC
Wire Description:	Vinyl Plastic Insulated Annealed Copper Cable
Wire Size:	14 AWG

Applications

- Heavy-Duty Automotive Fusing

Features and Benefits

- Accepts ATO® blade-style fuses (sold separately) up to 20 amps
- Interlocking fuse holder body lets you connect multiple fuse holders
- Heat-stabilized black nylon body has a UL 94 V-2 flammability rating
- 8" looped 14 AWG black lead wire allow simple in-line installation
- Gripping arms enable optional panel mounting