

ISF SERIES

250V SHOCK-SAFE AGC (3AG) PANEL-MOUNT GLASS FUSE HOLDER



03453LF2XP

Description

Compatible with AGC (3AG) glass fuses up to 20 amps, the ISF Series 250V Shock-Safe AGC (3AG) Panel-Mount Glass Fuse Holder features a low-profile body, finger-grip knob, and an anti-tease feature that eliminates circuit interruption when the knob is accidentally depressed.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/ISF

Specifications

Current Rating Continuous:	15A
Current Max:	20A
Fuse Type:	3AG Glass Fuses
Mounting Method:	Panel Mount
Housing:	PA66 GF30
Recommended Torque:	Mounting Torque: 15 Lbs.-In.
Max Voltage Rating:	250V

Applications

- Hole-Mounted Slow- or Fast-Blowing Automotive Fusing

Features and Benefits

- Accepts AGC (3AG) glass fuses up to 20 amps (sold separately)
- Shock-Safe fuse holder design eliminates the possibility of electrical shock, as defined in IEC standards 65 and 257
- Anti-tease feature eliminates circuit interruption when the knob is accidentally depressed
- Straight 3/16" Quick Connect terminals for easy wiring
- Low-profile body is easy to install to a panel without a screwdriver
- UL listed and CSA certified

Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
03453LF2XP	250V Shock-Safe AGC (3AG) Panel-Mount Glass Fuse Holder	3AG GLASS FUSES	PANEL MOUNT	20 AMPS	250 V