



RESISTANCE @ +25°C = 3,000 Ω ± 10%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)
 THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +135°C

| REV | REVISION RECORD | DATE | APP |
|-----|-----------------|----------|-----|
| --- | ISO RELEASE | 04/29/04 | DD |
| | | | |
| | | | |

| | | |
|----------|-------------|--|
| SCALE | NONE | © COPYRIGHT U.S. SENSOR CORP. 714-639-1000 www.ussensor.com NTC THERMISTOR P/N KC302J2K |
| DRAWN BY | DAN DANKERT | |
| DATE | 08/28/96 | |
| REV. | NONE | |
| LAYER | 0 OF 1 | |