



RESISTANCE @ +25°C = 2,000,000 Ω ± 10%
 RESISTANCE TEMPERATURE CURVE = "V4"
 TEMPERATURE COEFFICIENT @ +25°C = -4.85%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 4,288°K NOMINAL
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +300°C

---	ISO RELEASE	02/22/05	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLL INS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	05/15/98	NTC THERMISTOR
REV	NONE	P/N 205V4G1K
LAYER	0 OF 1	