

# MAXI® 152 SERIES

## 32V IN-LINE SPLASHPROOF BLADE FUSE HOLDER



01520003TXN941

### Description

The MAXI® 152 Series 32V In-Line Splashproof Blade Fuse Holder provides a simple way to install and protect a MAXI® blade-style fuse in a harsh automotive environment. The fuse holder cover and cable seals help to create a water-resistant fuse holder that protects the installed fuse (sold separately) against splashes and debris.

The MAXI® 152 Series is available in 60A and 80A MAXI® fuse holder configurations. The fuse holder bodies are also available with and without molded mounting tabs.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/MAXI152](https://www.littelfuse.com/MAXI152)

### Specifications

|                            |                     |
|----------------------------|---------------------|
| <b>Max Voltage Rating:</b> | 32VDC               |
| <b>Current Rating:</b>     | 60A, 80A            |
| <b>Fuse Type:</b>          | MAXI® Blade Fuse    |
| <b>Mounting Method:</b>    | In Line Fuse Holder |

### Applications

- Commercial Vehicle Circuit Protection
- Accessory Circuits

### Features and Benefits

- Available in 60A and 80A MAXI® fuse holder configurations
- Available with a splashproof IP54 or IP64 rating for water-resistant installation or with a waterproof rating of IP67 for installation in harsh environments
- Heat-resistant fuse holder cover protects the installed fuse (sold separately)
- Available with a UL 94 V-0 or UL 94 HB flammability rating
- Fuse holder body is available with and without molded mounting tabs
- Cable seals are available in various sizes to accommodate different wire gauges

# MAXI® 152 SERIES

## 32V IN-LINE SPLASHPROOF BLADE FUSE HOLDER

### Ordering Information

| PART NUMBER    | DESCRIPTION   | IGNITION PROTECTION | IGNITION PROOF | INGRESS RATING | WIRE SIZE                              |
|----------------|---|---------------------|----------------|----------------|--|
| 01520003TXN    | 32V In-Line Splashproof Blade Fuse Holder - 80A, IP64                                       | -                   | -              | -              | -                                      |
| 01520003TXN941 | 32V In-Line Splashproof Blade Fuse Holder - 80A, IP64, 2.5 to 6 mm <sup>2</sup> Cable Seals | HB                  | UL-94          | IP-64          | Recommended in MM <sup>2</sup> : 2.5-6 |
| 01520003TXN942 | 32V In-Line Splashproof Blade Fuse Holder - 80A, IP64, 6 to 10 mm <sup>2</sup> Cable Seals  | HB                  | UL-94          | IP-64          | -                                      |
| 01520003U      | 32V In-Line Fuse Holder Body - 80A, IP64  | HB                  | UL-94          | IP-64          | -                                      |
| 01520004Z      | 32V In-Line Fuse Holder Body with Mounting Tabs (Hole & Slot) - 60A                         | -                   | -              | -              | -                                      |
| 01520005Z      | 32V In-Line Fuse Holder Body with Mounting Tabs - 60A                                       | -                   | -              | -              | -                                      |
| 01520006Z      | 32V In-Line Fuse Holder Body - 60A  | -                   | -              | -              | -                                      |
| 01520008Z      | 32V In-Line Fuse Holder Body with Mounting Tabs - 80A                                       | -                   | -              | -              | -                                      |
| 01520009Z      | 32V In-Line Fuse Holder Body - 80A  | V-0                 | UL-94          | -              | -                                      |
| 01520010Z      | 32V In-Line Waterproof Blade Fuse Holder with Set Screw - 60A, IP67                         | V-0                 | UL-94          | IP-67          | -                                      |
| 01520903TXN    | Heat-Resistant Cover for MAXI® 152 Series 32V In-Line Blade Fuse Holder                     | -                   | -              | -              | -                                      |
| 01520903U      | Heat-Resistant Cover for MAXI® 152 Series 32V In-Line Blade Fuse Holder                     | -                   | -              | -              | -                                      |
| 279.6805.0602  | 32V In-Line Blade Fuse Holder - 80A, 6 to 10 mm <sup>2</sup> Cable Seals                    | V-0                 | UL-94          | -              | 6-10 mm <sup>2</sup>                   |
| 279.6850.0402  | 32V In-Line Splashproof Blade Fuse Holder - 80A, IP54, 4 mm <sup>2</sup> Cable Seals        | V-0                 | UL-94          | IP-54          | 4 mm <sup>2</sup>                      |
| 279.6850.0602  | 32V In-Line Splashproof Blade Fuse Holder - 80A, IP54, 6-10 mm <sup>2</sup> Cable Seals     | V-0                 | UL-94          | IP-54          | 6-10 mm <sup>2</sup>                   |
| 279.6850.1602  | 32V In-Line Splashproof Blade Fuse Holder - 80A, IP54, 16 mm <sup>2</sup> Cable Seals       | V-0                 | UL-94          | IP-54          | 16 mm <sup>2</sup>                     |
| 868-095        | 12-14 Gauge Cable Seal for MAXI® 152 Series Fuse Holder                                     | -                   | -              | -              | -                                      |
| 868-096        | 8-10 Gauge Cable Seal for MAXI® 152 Series Fuse Holder                                      | -                   | -              | -              | -                                      |