



Product Overview

PolySwitch BD280 Bladed Contact Resettable Overcurrent Protection

The Littelfuse Reflowable Thermal Protection (RTP) device is a low resistance, robust surface mountable thermal protector. It has a set open temperature and can be installed using reliable, lead-free, Surface Mount Device (SMD) assembly and reflow processes.

PolySwitch BD280 Bladed Contact



KEY FEATURES

- 2.8mm terminals
- Latches on first trip
- PTC resistance switching action
- Constant wattage power dissipation when tripped
- Solid state construction
- Probe points
- Bright color coded housing
- Low thermal derating

APPLICATIONS

- Automotive and heavy trucks circuits
- Wiring harness protection
- 12V power outlets
- Intermittent duty circuits (with high inrush current)
- DC motor circuits
power window, power seat, power door lock, fuel & trunk door release, others
(needing to survive lock rotor conditions)

BENEFITS

- Easy to implement, reliable solid state resettable overcurrent protection
- Reduces fault energy delivered to the wiring and loads
- Long, safe performance life
- Resilient at minimum and maximum voltage
- Not subject to change in calibration due to rough handling or high shock and vibration
- Facilitates fault finding
- Less chance of mis-installation
- Color recognition inspection possible
- Offers resettable overcurrent protection even in vehicle underhood applications

FUNCTION

- Directly replaces mini-sized automotive fuses and circuit breakers
- No cycling into short or overload
- No contacts to erode or weld together
- Virtually constant power consumption across voltage range 4V to 16V
- Very high resistance to shock and vibration
- Easier diagnostics
- Easily recognizable current rating
- Passes more current at higher temperatures than bi-metal circuit breakers

PolySwitch BD280 Bladed Contact


ELECTRICAL CHARACTERISTICS

Nominal Operating Voltage:	14V
Maximum Operating Voltage:	16V
Current Ratings:	10A, 15A, 20A, 25A, 30A
Cycle Life:	1,000 cycles @ 100A fault current
Trip Endurance:	1,000 hours @ 14V
Load Dump:	Per ISO 7337-1

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature:	-40°C to +125°C
Vibration:	Meets or exceeds SAE J553
Mechanical Shock:	Meets or exceeds SAE J553
Thermal Shock:	Meets or exceeds SAE J553
Humidity:	Meets or exceeds SAE J553
Cap Retention:	90N (20lbf)

THERMAL DERATING



PolySwitch bladed devices exhibit much less roll-off at high temperatures which allows for their use in underhood applications.

INTERRUPT CURRENT AND VOLTAGE DROP MEETS OR EXCEEDS SAE J553


Current Ratings (A)	I Interrupt* (A)	Max. Voltage Drop (mV) @ Current Rating
10	225	180
15	300	160
20	450	135
25	450	115
30	450	105

* Tested to 5 cycles

ENVIRONMENTAL SPECIFICATIONS

Box Material:	PBT meeting UL V-0 requirements
Terminal Material:	Brass with Tin over Nickel plating

TRIP CHARACTERISTICS




PolySwitch BD280 device latches after the first overcurrent trip, whereas Type II bi-metal circuit breakers typically cycle several times.


PolySwitch BD280 Bladed Contact

PART NUMBERS, STYLES AND DIMENSIONS

Part Numbers	Current Ratings	Body Style	mm Min/Max (inch approx.)								
			A	B	C	D	E(x2)	F	G	H	I
BD280-1130-10/16	10A	1	29.5/30.1 (1.173/1.185)	8.7/9.3 (0.343/0.366)	10.75/11.25 (0.423/0.443)	6.05/6.65 (0.238/0.262)	2.55/3.05 (0.1/0.12)	3.3/3.9 (0.13/0.154)	3.4/4 (0.134/0.157)	1.7/2.3 (0.067/0.091)	10.9/11.5 (0.429/0.453)
BD280-1130-15/16	15A	1	29.5/30.5 (1.173/1.185)	8.7/9.3 (0.343/0.366)	10.75/11.25 (0.423/0.443)	6.05/6.65 (0.238/0.262)	2.55/3.05 (0.1/0.12)	3.3/3.9 (0.13/0.154)	3.4/4 (0.134/0.157)	1.7/2.3 (0.067/0.091)	10.9/11.5 (0.429/0.453)
BD280-1130-20/16	20A	1	29.5/30.1 (1.173/1.185)	8.7/9.3 (0.343/0.366)	10.75/11.25 (0.423/0.443)	6.05/6.65 (0.238/0.262)	2.55/3.05 (0.1/0.12)	3.3/3.9 (0.13/0.154)	3.4/4 (0.134/0.157)	1.7/2.3 (0.067/0.091)	10.9/11.5 (0.429/0.453)
BD280-1927-25/16-W	25A	2	26.65/27.35 (1.049/1.077)	8.6/9.2 (0.339/0.362)	10.75/11.25 (0.423/0.443)	6.05/6.65 (0.238/0.262)	2.55/3.05 (0.1/0.12)	1.8/2.2 (0.071/0.087)	3.5/3.9 (0.138/0.154)	1.7/2.3 (0.067/0.091)	19/19.4 (0.748/0.764)
BD280-1927-30/16-W	30A	2	26.65/27.35 (1.049/1.077)	8.6/9.2 (0.339/0.362)	10.75/11.25 (0.423/0.443)	6.05/6.65 (0.238/0.262)	2.55/3.05 (0.1/0.12)	1.8/2.2 (0.071/0.087)	3.5/3.9 (0.138/0.154)	1.7/2.3 (0.067/0.091)	19/19.4 (0.748/0.764)



Body Style 1



Body Style 2

Notice:

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.