

PGT-0400 SERIES

Ground-Fault Relay Test Unit



Description

The PGT-0400 is a ground-fault-relay test unit designed to test current pickup level, time-delay and coordination of ground-fault protection.

The tester injects current through the window of installed ground-fault current transformers to verify the operation of ground-fault monitors and relays.


Used on substations, motor control centers (MCCs), central distribution panels, switchboards, and test benches to verify relay operation.

The PGT-0400 tests the entire ground-fault circuit including current transformers, wiring, ground-fault relay and the operation of the interrupting device. It is recommended to test every relay and its current interrupting device annually.

Features & Benefits

FEATURES	BENEFITS
Adjustable Current Setpoint	Current range is 0.5 to 9.9 A
Adjustable Time Duration Setpoint	Duration range is 0.1 to 9.9 s, or continuous output
Small Form Factor	Light weight and compact for portability
Remote Test Input	Allows test to be initiated from another location

Wiring Diagram



Ordering Information

CATALOG/ SYSTEM NUMBER	CONTROL POWER
PGT-0400	120 Vac

Specifications

Input Voltage	84–134 Vac, 50/60 Hz, 80 VA
Dimensions	H 219 mm (8.6"); W 99 mm (3.9"); D 143 mm (5.6")
Output Current Settings	0.5–9.9 A
Output Duration Settings	0.1–9.9 s or continuous
Output Voltage	5.0 Vac maximum
Conformally Coated	Standard feature
Warranty	5 Year
Mounting	Surface, Panel