

## Terminal Type 2

RoHS



### Terminal Loks

| Description<br>Beschreibung                    | Wire Diam.<br>Drahtdurchmesser | Type of terminal loks<br>Verriegelungstyp |
|--|--------------------------------|---|
| For part number/<br>für Teilenummer:<br>354505 | 0,50 - 2 mm <sup>2</sup>       | 8   |

| Part Number<br>Teilenummer  | Description<br>Beschreibung | Wire Diam.<br>Drahtdurchmesser   | Material                                     |
|---|-----------------------------|--|--|
| 913-064 (Reeled/auf Spule per 1200 pcs)<br>0913064001 (Single per 250 pcs)  | Female 8,0 mm               | 2.09-3.32 mm <sup>2</sup> / 14-12AWG<br>2.09-3.32 mm <sup>2</sup> / 14-12AWG | Silver plated brass /<br>Messing, versilbert |
| 913-068-001 (Reeled/auf Spule per 1200 pcs)<br>913-068 (Single per 200 pcs) | Female 8,0 mm               | 5.37mm <sup>2</sup> / 10AWG<br>5.37mm <sup>2</sup> / 10AWG                   | Silver plated brass /<br>Messing, versilbert |

## Terminal Type 3

RoHS



### Terminal Loks

| Description<br>Beschreibung  | Wire Diam.<br>Drahtdurchmesser | Type of terminal loks<br>Verriegelungstyp |
|--|--------------------------------|---|
| For part number/<br>für Teilenummer:<br>354506 / 354508 /<br>354535 / 354536 | -                              | 1   |
| For part number<br>für Teilenummer:<br>354507                                | -                              | 2   |

| Part Number<br>Teilenummer                                       | Description<br>Beschreibung | Wire Diam.<br>Drahtdurchmesser   | Material                             |
|--|-----------------------------|--|--------------------------------------|
| 913-053 (Reeled per 2000 pcs)<br>0913053001 (Single per 250 pcs) | -                           | 0.5-0.8 mm <sup>2</sup> / 18-20AWG<br>0.5-0.8 mm <sup>2</sup> / 18-20AWG     | Tin plated brass / Messing, verzinkt |
| 913-253 (Reeled per 3000 pcs)                                    | -                           | 0.5-1.00 mm <sup>2</sup> (metric)  | Tin plated brass / Messing, verzinkt |
| 913-065 (Reeled per 2100 pcs)<br>0913065001 (Single per 250 pcs) | -                           | 1.33-2.09 mm <sup>2</sup> / 14-16AWG<br>1.33-2.09 mm <sup>2</sup> / 14-16AWG | Tin plated brass / Messing, verzinkt |
| 913-265 (Reeled per 2500 pcs)                                    | -                           | 1.1-2.50 mm <sup>2</sup> (metric)  | Tin plated brass / Messing, verzinkt |
| 913-055 (Reeled per 1900 pcs)<br>0913055001 (Single per 250 pcs) | -                           | 3.32-5.37 mm <sup>2</sup> / 10-12AWG<br>3.32-5.37 mm <sup>2</sup> / 10-12AWG | Tin plated brass / Messing, verzinkt |
| 913-255 (Reeled per 15000 pcs)                                   | -                           | 4.0-6.0 mm <sup>2</sup> (metric)   | Tin plated brass / Messing, verzinkt |