



PART NUMBER	PACKAGING
LR222E0J-1	BULK
LR222E0J-2	TAPE & REEL

RESISTANCE @ +25°C = 2,200 Ω ± 5%
 RESISTANCE/TEMPERATURE CURVE = SEE LR222E0J R-T TABLE
 BETA "β" (+25 TO +85°C) = 3,400°K NOMINAL
 POWER RATING = 320 mW
 TEMPERATURE RATING = -40 TO +125°C

PACKAGING: SEE TABLE

ROHS COMPLIANT

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	04/27/17	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	04/27/17	
REV.	NONE	
LAYER	0 OF 2	NTC CHIP THERMISTOR P/N LR222E0J-