



RESISTANCE @ +25°C = 20,000 $\Omega \pm 10\%$
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25C = -4.4%/°C NOMINAL
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL
 MAXIMUM TEMPERATURE RATING = +220°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	11/02/05	DD
"A"	TAB WAS $0.019'' \pm 0.004''$, LENGTH WAS $0.140'' \pm 0.010''$ & DIA WAS $0.065'' \pm 0.004''$	11/02/05	DD

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com
DRAWN BY T. WILFONG	
DATE 08/08/95	NTC THERMISTOR
REV. "A"	P/N SM203J1K
LAYER 0 OF 2	