



RESISTANCE @ +25°C = 2,186 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "E1"  
 BETA "β" (0 TO +50°C) = 3,320°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -3.82%/°C NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM  
 MAXIMUM TEMPERATURE RATING = +220°C

\*\*\* ROHS COMPLIANT \*\*\*

PACKAGING: BULK

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	01/27/14	DD

SCALE NONE	U.S. SENSOR CORP. www.ussensor.com 714-639-1000 © COPYRIGHT
DRAWN BY DAN DANKERT	
DATE 01/27/14	NTC THERMISTOR
REV. NONE	P/N SM222E1K
LAYER 0 OF 1	