



RESISTANCE @ +25°C = 10,000 ± 5%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +105°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

---	ISO RELEASE	07/11/03	DD
"A"	PROBE LENGTH WAS 5" LONG	08/28/01	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	U.S. SENSOR CORP. 1832 W. COLL INS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com
DRAWN BY DAN DANKERT	
DATE 08/23/01	NTC THERMISTOR PROBE
REV. "A"	P/N USP3275
LAYER 0 OF 2	