


# USP18967 Thermistor Probe




## Description

Littelfuse offers Copper clip-on pipe probe housings suitable for a wide range of temperature sensing applications. If the dimensions on this product won't work for your requirements, please contact us for further assistance.

## Features

- Tight Tolerance
- Supplied with a Copper Plated Clip designed to affix to a 0.875" Diameter Pipe
- Moisture Resistant
- 105°C Max Operating Temperature

## Dimensions




Dimensions in inches.

A	B	C	D	E	F
0.233" Nom	0.985" Nom	0.660" Nom	0.830" Nom	0.810" Nom	0.030" Nom

G	H	I	J	K
0.787" Nom	0.394" Nom	240" ±10"	0.164" Nom	Strip: 0.250" ±0.070"

## Part Numbering System



**Note:** Not all combinations of Part Number codes are available. Contact Littelfuse for details.

## Specifications

Part Number	Resistance Ohms @25°C	Resistance Tol. ± % @ 25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 25-85°C	Temperature Rating (°C)
USP18967	10000	1	J	-4.4	3977	-55 to +105

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)