



RESISTANCE @ +25°C = 10,000 Ω ± 1%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 MAXIMUM TEMPERATURE RATING = +105°C

MOUNTING-HOLE DIAMETER = 0.145" NOMINAL  
 MOUNTING-HOLE STUD-SIZE = #6

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	09/03/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP.
DRAWN BY	DAN DANKERT	
DATE	09/03/03	© COPYRIGHT 714-639-1000 www.ussensor.com
REV.	NONE	THERMISTOR PROBE
LAYER	0 OF 2	P/N USP4261