



RESISTANCE @ +25°C = 10,000 Ω ± 5%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 MAXIMUM TEMPERATURE RATING = +105°C

LEAD WIRES: 28 AWG, STRANDED CONDUCTOR,  
 SINGLE CONDUCTOR, PVC INSULATED

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	LEAD WIRE LENGTH WAS 3" ± 0.50"	09/21/10	DD
NONE	RELEASE TO PRODUCTION	04/06/10	DD
REV		REVISION RECORD	DATE APP

SCALE	NONE	<b>U.S. SENSOR CORP.</b> 1832 W. COLLINS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	04/06/10	
REV.	"A"	
LAYER	0 OF 2	
		NTC THERMISTOR PROBE
		P/N USP10997