


2

1



B

B

Mechanical Dimensions :

A	B	C	D	E
0.063" ± 0.007" (1.6002 ± 0.1778mm)	0.0315" ± 0.007" (0.8001 to 0.1778 mm)	0.0394" Max (1.0007 mm Max)	0.0157" ± 0.010"(2X) (0.3987 ± 0.254mm (2X))	Solder Plated Terminations

Electrical Specifications :

Resistance (25 °C) Ω	Resistance Tolerance, ±%	Temp, Coefficient (%/ °C)	Beta(K)	Temp Rating(°C)	Power Rating(V)	Packaging
100 to 100000	1 to 10	3.31 to 4.4	2000~5000	-55 ~ +150	40~400	Tape & Reel

A

A

Rev	Description	By	Date	ECO NO
A	Initial Release	RKM	04/04/2023	
Revision History				
Reference Legacy No.		USPxxxx REV x		

Project Code XXXXXX			
Units Inch(mm)	Division IBU - Temperature Sensors		
General Tolerances 0.X = ± 0.X 0.XX = ± 0.XX 0.XXX = ± 0.XXX	Title End Banded NTC Thermistor Chips-0603		
Drawn By RKM	Finished Product Part Number NSRB		Rev A
Date 04/04/2023	Internal No. NSRB	Size A	Sheet 1 of 1

2

1