




SECTION B - B



SECTION A - A



METRIC
ASSEMBLY

- NOTES:
 1. MATERIALS:
 COVER: CRYSTAL-CLAEER POLYCARBONATE
 BODY: BLACK POLYAMIDE, GLASS FIBER REINFORCED
 CONTACT SECURING: WHITE POLYAMIDE, GLASS FIBER REINFORCED
 CONTACTS: TIN PLATED BRASS, PLATING THICKNESS 8-10u

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
		UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES		
		UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.		
		⊙ DENOTES CRITICAL CHARACTERISTICS.		
		CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
		ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
		CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		

COPIES TO		MATL SPEC		REFER TO NOTES	
LTR	DATE	REVISION	CHK	APD	
1	9	18			
2	10	19			
3	12	20			
4	13	21			
5	14	23			
6	15	33			
7	16	43			
8	17	53			
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)		TOLERANCE		GRAMS/PIECE	
DIMENSION		0.5 - 3	UP TO OVER	3 - 6	UP TO OVER
				6 - 30	UP TO OVER
				30 - 120	UP TO OVER
				120 - 400	UP TO OVER
					±0.3 ±0.5
3RD ANGLE PROJECTION		TITLE		AT0 BLOCK 5 POSITIONS, HORIZONTAL CONTACTS	
LITTLEFUSE		REVISION		DRWG. NO.	
LIPA CITY, BATANGAS, PHILIPPINES		A		03500417Z	
		OUTLINE			