


PART No.	WIRE GA. / COLOR	"A" (REF)	"B"	"C"
OFNY0002ZXJ	# 12 ORANGE	266.7 (10.5)	9.65±2 (.38)	9.65±2 (.38)



- NOTES:
1. DIMENSION "A" MEASURED WITH FUSE INSTALLED.
  2. MAX RATING: 30A, 32VDC.
  3. MAX. TEMPERATURE: 80°C.
  4. WIRE: COPPER STRANDED, GXL.
  5. CONTACTS: C1100 ALLOY.
  6. CRIMP: MUST MEET USCAR 21 STANDARD.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE

(S) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT IS TO BE DETERMINED BY THE CUSTOMER OR SUPPLIER. INSPECTOR MUST FOLLOW THE INSTRUCTIONS.

CPK DENOTES CP DIMENSIONS--MINIMUM CP VALUE

(S) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT IS TO BE DETERMINED BY THE CUSTOMER OR SUPPLIER. INSPECTOR MUST FOLLOW THE INSTRUCTIONS.

CPK DENOTES CP DIMENSIONS--MINIMUM CP VALUE

(S) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT IS TO BE DETERMINED BY THE CUSTOMER OR SUPPLIER. INSPECTOR MUST FOLLOW THE INSTRUCTIONS.

COPIES TO		MATERIAL SPEC		FINISH	
1	9	DRW	18	DATE	09/05/08
2	10	CHK	19	SCALE	1=1
3	12	APPD	20	DATE	
4	13		21	DATE	
5	14		23	DATE	
6	15		33	DATE	
7	16		43	DATE	
8	17		53	DATE	

TOLERANCE UNLESS OTHERWISE SPECIFIED  
TWO PLACE DEC ±.01  
THREE PLACE DEC ±.005  
ANGULAR ±1°

TITLE: FUSEHOLDER, INLINE (WITH FUSE)

LTR	REVISION	CHK	APD
A	000490ER-RELEASED 9/05/08	DHM	

REVISION: A

DRWG. NO. OFNY0002ZXJ

OUTLINE

DES PLAINES, ILLINOIS 60016

