



METRIC COMPONENT

CABLE SEAL FOR OUTPUT WIRE				
PART NAME	PART NUMBER	D1	D2	COLOR
Cable Seal -10 ~16 mm sq	0HBFA001SEALB	5.0	7.1	BLUE
Cable Seal -6~10 mm sq	0HBFA001SEALY	3.3	5.7	YELLOW
Cable Seal -BLIND	0HBFA001SEALC	N/A	N/A	GREY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
<S>	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
----	--------------	-------------	-------	-----

BILL OF MATERIAL

DATE	REVISION	CH	AP
3/19/15	1	K	D

COPIES TO	MATL SPEC	Silicone Rubber,BLUE		
1 9 18	FINISH			
2 10 19	DRW	xxx	DATE	3/19/15
3 12 20	CHK		DATE	
4 13 21	APPD		DATE	
5 14 23				FINISH GOOD WT
6 15 33				GRAMS/PIEC
7 16 43				
8 17 53				

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)					
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400
TOLERANCE	±0.05	±0.05	±0.1	±0.15	±0.2

TITLE	Cable seal 10-16 mm2 (BLUE)
REVISION	DRWG. NO.
A	OL-0HBFA001SEALB

REV: 01/15  
 312001, CHINA, 0512-87615185