


Ø50.8 ± 0.38
[Ø2.00 ± 0.015]

6.4 ± 0.08
[0.25 ± 0.003]



41.3 ± 0.89
[1.63 ± 0.035]


10.3 ± 0.13
[0.41 ± 0.005]

180.9 ± 2.29
[7.12 ± 0.090]

133.4 ± 1.52
[5.25 ± 0.060]

85.7 ± 0.76
[3.38 ± 0.030]

13.5 ^{+1.57}_{-0.00}
[0.53 ^{+0.062}_{-0.000}]



REVISION		
REV	DATE	DESCRIPTION
A	10/14/22	525789GCP - RELEASE MRY

1	NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
---	----	--------------	-------------	-------	-----

BILL OF MATERIAL

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE
●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
⊠	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC	FINISH
-----------	--------

DRW JMOLER	DATE 10/13/2022	SCALE NTS	FINISH GOOD WT GRAMS/PIECE
---------------	--------------------	--------------	-------------------------------

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION	
-------------------------	--

TITLE	SPFJ 250-400A OUTLINE
-------	-----------------------

Littelfuse CHICAGO, ILLINOIS 60631	REVISION A	DRWG NO. OL-SPFJ400	SHEET 1 OF 1
--	----------------------	-------------------------------	--------------