





METRIC

COMPONENT

[illegible]

COPIES TO			MATL SPEC			2.0mm MS PLATE				
1	9	18	FINISH ZINC CHROMATE PLATED (t = 3-8 microns)							
2	10	19								
3	12	20								
4	13	21								
5	14	23	DRW	FYUE	DATE	20/Oct/16	SCALE	1:1		
6	15	33	CHK		DATE		SUPER DR			
7	16	43	APPD		DATE		FINSH GOOD WT			
8	17	53				GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)										
DIMENSION		UP TO		OVER		UP TO		OVER		
		0.5 - 3		3 - 6		6 - 30		30 - 120		
TOLERANCE		±0.1		±0.1		±0.2		±0.3		
3RD ANGLE PROJECTION									UP TO 120	OVER 120 - 400
									±0.5	
TITLE			METAL BRACKET							
			(for HWB18, 12&6)							
			REVISION		DRWG. NO.		OUTLINE			
			B		868 - 068					
										
LIPA CITY, BATANGAS, PHILIPPINES										