




SECTION A - A

NOTES:

1. MATERIALS:
COVER: CRYSTAL-CLAEER POLYCARBONATE
BODY: BLACK POLYAMIDE, GLASS FIBER REINFORCED
CONTACT SECURING: WHITE POLYAMIDE, GLASS FIBER REINFORCED
CONTACTS: TIN PLATED BRASS, PLATING THICKNESS 8-10u
2. INSERTION FORCE: 20-50N
3. EXTRACTION FORCE: 12-50N

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M	
BILL OF MATERIAL					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS () ARE INCHES					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.					
		DENOTES CRITICAL CHARACTERISTICS.			
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

[illegible]