


MM IN
 10
 2.76 0.11
 1.52 0.06
 2.03 0.08
 2.28 0.09
 3.17 0.125
 3.55 0.14
 4.82 0.19
 9.14 0.36
 9.39 0.37
 15.74 0.62
 46.98 1.85
 46.99 1.85

EX-14258

APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259

956-4104



NOTES:

1 SHUTTER TYPE SEAL ON LOCK FACE

2 ALL STEEL PARTS PLATED

METRIC

RATINGS AT 12 VDC

ACC CIRCUIT	10 AMPS
IGN CIRCUIT	10 AMPS
ST CIRCUIT	5 AMPS

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	ATERIAL	DRAWN	HE REGISTERED	SCALE	DATE DRAWN
								—H—	MF	 1-26-79	1:1	3-15-66
				M	ECN 00137	3/1/00	MA	FIN CH —H—	 Cole Hersee Co. 90 DEGREE VIEW FROM RIGHT			DATE BLUEPRINT
				L	LABOR ZINC 125254	12/22/92	JH					
				K	MOLDS INC	8/15/87	PS	TOLERANCES	4 - POSITION			956-4104
				J	REDRAWN	1/18/79	JH	FRACTIONAL ± DECIMAL ± .25	IGNITION & START SWITCH			

CH 188 (4 78)