


SCALE 2 : 1



METRIC
COMPONENT

CABLE SEAL FOR OUTPUT WIRE				
PART NAME	PART NUMBER	D1	D2	COLOR
Cable Seal -10 ~16 mm sq	0HBFA001SEALB	5.0	7.1	BLUE
Cable Seal -6~10 mm sq	0HBFA001SEALY	3.3	5.7	YELLOW
Cable Seal -BLIND	0HBFA001SEALC	N/A	N/A	GREY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
<S>	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

BILL OF MATERIAL				QTY/M	U/M
NO	COMPONENT NO	DESCRIPTION			
		MATERIAL SPEC			
		Silicone Rubber,BLUE			
		FINISH			
1	9	18			
2	10	19			
3	12	20			
4	13	21	DRW	xxx	DATE
5	14	23	CHK		DATE
6	15	33	APPD		DATE
7	16	43			FINISH GOOD WT
8	17	53			GRAMS/PIEC
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)					
DIMENSION		0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE		±0.05	±0.05	±0.1	±0.15
3RD ANGLE PROJECTION		TITLE			
		Cable seal 10-16 mm2 (BLUE)			
		Littelfuse		REVISION	
		SUZHOU, CHINA, 0512-87613189		DRWG. NO.	
				OL-0HBFA001SEALB	