


PART No.	WIRE GA. / COLOR	"A"
0FNY0001ZXJ	#14 BLACK	203.2±5 (8.0)



DETAIL B

- NOTES:
1. MAX FUSE RATING: 20A, 32VDC.
 2. MAX. OPERATING TEMPERATURE: 80°C.
 3. WIRE: COPPER STRANDED, UL 1015.
 4. CONTACTS: C2680 ALLOY.
 5. CRIMP: MUST MEET USCAR 21 STANDARD.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.		DENOTES CRITICAL CHARACTERISTICS.		DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. (PROCEDURE FOR MEASUREMENT OF CPK VALUE IS LOCATED IN THE INSTRUCTIONS.)		DENOTES CP DIMENSIONS.-MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SPECIFIED IN THE INSTRUCTIONS AND INITIALLY LOCATED TO THE DRAWING FOR MAXIMUM TOOL LIFE.	
LTR		REVISION		CHK		APD			
A		000490ER-RELEASED 9/05/08							