




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	C	ECN #08348 ADDED NOTE 4	06/17/2008	LIZ
	D	ECN #09059 LEVER BRIGHT CHROME	01/19/2009	LIZ
	E	ECO #520819 UPDATE "CH" BRAND MARKING	05/23/2019	J. LI



- NOTES
1. ALL STEEL PARTS PLATED
 2. ALL DIMENSIONS ARE REFERENCE ONLY
 3. LOCK OUT BRACKET, LEVER, TWO MOUNTING SCREWS & INSTRUCTION SHEET SHIPPED IN PLASTIC BAG
 4. FOR USE WITH 0.312 [7.93] DIAMETER LOCK SHANK

INTERPRET DRAWING TO ANSI/ASME Y14.5-1994.				
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL			
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL			
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
DIMENSION; MM TOLERANCES UNLESS OTHERWISE SPECIFIED ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100 TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°				
-	NAME	DATE	 Expertise Applied Answers Delivered	
DRAWN	J. LI	05/23/2019		
CHECKED	-	-		
	-	-		
			TITLE LOCK OUT KIT FOR MASTER DISCONNECT SW	
FORM NO: CVP-PE40-0004 REV A				
THIRD ANGLE PROJECTION			SIZE B	
				
DO NOT SCALE DRAWING			DWG. NO. 24505	
SCALE 1:1			REV. E	
			SHEET 3 OF 9	