





MM	IN
2.5	0.09
2.28	0.09
2.05	0.08
1.82	0.07
1.59	0.06
1.36	0.05
1.13	0.04
0.90	0.03
0.67	0.02
0.44	0.01
0.21	0.00

57000-01
57000-05

ROCKER, WHITE
BEZEL, STEEL, NICKEL PLT, BRIGHT FIN.
TERM. INSUL., MOLDED PHENOLIC
MALE BLADE TERM., BRASS, SAE J858.
TYPE IB (2 REQ'D)



MOUNTING HOLE DETAIL



NOTE:

1. HEAVY DUTY
2. SILVER CONTACT RIVETS & SILVER CONTACT PAD
3. 25 AMPS AT 12 VDC LAMP LOAD

METRIC

DO NOT SCALE

[illegible]

CH-188(4-78)