





MM	IN
7.25	.010
7.28	.020
7.70	.030
8.11	.040
17.01	.070
17.27	.080
21.08	.090
27.86	.100
27.94	.110
30.27	.120
31.29	.130
36.83	.140
39.87	.150

57001-01
57001-05



METRIC

NOTE:

1. HEAVY DUTY
2. SILVER CONTACTS
3. 25 AMPS AT 12 VDC LAMP LOAD

5700I-05 SAME AS 5700I-01, EXCEPT
BEZEL, NICKEL PLATE, DULL FINISH

DO NOT SCALE

[illegible]

CH-188(4-78)