






LTR	DATE	REVISION	CHK	APD
A	01/22/14	510030ERA-RELEASE FYUE		
B	07/18/14	510793ECA-ADD DIMENSTONS FYUE		



-				
-				
-				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO		MATL SPEC		
		Mapex PA66 A0520FN-03 (30%GF)		
1 9 18	FINISH NONE			
2 10 19				
3 12 20	DRW FYUE DATE 01/22/14 SCALE 1:1			
4 13 21				
5 14 23	CHK DATE SUPER DR			
6 15 33				
7 16 43	APPD DATE FINSH GOOD WT			
8 17 53				
GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)				
DIMENSION	0.5 - 3	UP TO 3 OVER 3 - 6	UP TO 6 OVER 6 - 30	UP TO 30 OVER 30 - 120
TOLERANCE	+0.1	+0.1	+0.2	+0.3
3RD ANGLE PROJECTION				
TITLE		BASE		
CHICAGO, USA 773-628-1000		REVISION B	DRWG. NO. OL-868-163	OUTLINE

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)